

Product End of Life

Vertiv™ PowerIT Basic and Metered Upgradeable Rack PDU Models



Key dates:

- **End of Sale (and EOL):** July 1, 2025
- **End of Production:** August 1, 2025
- **End of Service:** July 1, 2030

Effective July 1st, 2025 select Vertiv™ PowerIT Basic and Metered Upgradeable Rack PDU models will be discontinued. The last day orders will be accepted is June 30th, 2025.

A detailed list of the affected products is shown below. No replacements will be offered. Please contact inside sales at 1-800-432-3219 to identify an appropriate replacement or Engineer-To-Order (ETO) solution.

Vertiv will provide existing customers with support and technical assistance on a reasonable commercial basis after final sale. The standard warranty remains in effect for products covered in this notice.

Part No.	Model No.
GI10001L	MG01X4B1-12L193-3PS56B2A10-S
GI10002L	MG01X2R1-12L193-3PS56B2H10-S
GI10003L	MG01X4W1-36PT63-3PS6B2A10-S
GI10004L	MG01X2R1-16PB43-3PS6B2H10-S
GI10005L	MG01X4W1-30PN63-3PS56B2A10-S
GI10006L	MG01X4W1-36PT63-3PS6C2A10-S
GI10007L	MG01X2R1-16PB43-3PS6C2H10-S
GI10008L	MG01X4W1-30PN63-3PS56C2A10-S
GI10009L	MG01X4W0-42PZ63-2PS56C2A10-S
GI10010	MG01X4B0-18PB63-2PS6B2A10-S
GI10011	MG01X4W1-42IZ63-3PS6B2A10-S
GI10012	MG01X4W1-42IZ63-3PS6C2A10-S
GI10014	MG01X4W1-42IZ63-3PS56C2A10-S
GI10015L	MG01X4B1-24PBB3-3PS56B2A10-S
GI10016	MG01X4B1-36IT63-3PS6B2A10-S
GI10017	MG01X4W1-48C133-3PS56B2A10-S
GI10018L	MG01X4B0-26PJ63-2PS6B2A10-S
GI10019L	MG01X4B1-26PJ63-3PS6B2A10-S
GI10020L	MG01D4B1-12L193-3PS56B2A10-S

Part No.	Model No.
GI10021L	MG01D2R1-12L193-3PS56B2H10-S
GI10022L	MG01D4W1-36PT63-3PS6B2A10-S
GI10023L	MG01D2R1-16PB43-3PS6B2H10-S
GI10024L	MG01D4W1-30PN63-3PS56B2A10-S
GI10025L	MG01D4W1-36PT63-3PS6C2A10-S
GI10026L	MG01D2R1-16PB43-3PS6C2H10-S
GI10027L	MG01D4W1-30PN63-3PS56C2A10-S
GI10028L	MG01D4W0-42PZ63-2PS56C2A10-S
GI10029L	MG01D4B0-18PB63-2PS6B2A10-S
GI10030	MG01D4W1-42IZ63-3PS6B2A10-S
GI10031	MG01D4W1-42IZ63-3PS6C2A10-S
GI10032	MG01D4W1-42IZ63-3PS56B2A10-S
GI10033	MG01D4W1-42IZ63-3PS56C2A10-S
GI10034L	MG01D4B1-24PBB3-3PS56B2A10-S
GI10035	MG01D4B1-36IT63-3PS6B2A10-S
GI10036	MG01D4W1-48C133-3PS56B2A10-S
GI10037L	MG01D4B0-26PJ63-2PS6B2A10-S
GI10038L	MG01D4B1-26PJ63-3PS6B2A10-S
GI10039	MG01D4W0-20UKR3-3PS6B2A10-S

Part No.	Model No.
GI10040	MG01D4W1-20SKR3-3PS6B2A10-S
GI10041	MG01D4W0-20UKR3-2PS6B2A10-S
GI10042	MG01D4W0-20SKR3-2PS6B2A10-S
GI10043L	MG01X1R0-10L133-2PS6B2H10-S
GI10045L	MG01X1R1-10L133-3PS6B2H10-S
GI10046L	MG01X1R1-10L133-3PS6C2H10-S
GI10047L	MG01X1R1-08P443-3PS6B2H10-S
GI10048L	MG01X1R1-08P443-3PS6C2H10-S
GI10049L	MG01D1R0-10L133-2PS6B2H10-S
GI10051L	MG01D1R1-10L133-3PS6B2H10-S
GI10052L	MG01D1R1-10L133-3PS6C2H10-S
GI10053L	MG01D1R1-08P443-3PS6B2H10-S
GI10054L	MG01D1R1-08P443-3PS6C2H10-S
GI10056L	MG01X4W1-30PN63-3PS56B2A10-S-A
GI10057L	MG01X5W1-42PZ63-3PS56B2A10-S-A
GI10058L	MG01D4W1-30PN63-3PS56B2A10-S-A
GI10059L	MG01D5W1-42PZ63-3PS56B2A10-S-A
GI10060L	MG01D1R0-09P633-2PS56B2H10-S
GI10061L	MG01D2R0-18PB63-2PS56B2H10-S
GI10062L	MG01D4B0-18PB63-2PS56B2A10-S
GI10064	MG01D4B0-42IZ63-2PS56B2A10-S
GI10065	MG01D4B0-48C133-2PS56B2A10-S
GI10066L	MG01D4W0-42PZ63-2PS56B2A10-S
GI10067L	MG01D5W0-42PZ63-2PS56B2A10-S-A
GI10068L	MG01X1R0-09P633-2PS56B2H10-S
GI10069L	MG01X2R0-18PB63-2PS56B2H10-S
GI10070L	MG01X4B0-18PB63-2PS56B2A10-S
GI10073	MG01X4B0-48C133-2PS56B2A10-S
GI10074L	MG01X4W0-42PZ63-2PS56B2A10-S
GI10075L	MG01X5W0-42PZ63-2PS56B2A10-S-A
GI10093	MG01X4B0-36CF13-2PS6B2A10-S
GI10096	MG01D4B0-36CF13-2PS56B2A10-S-A
GI10097	MG01D4B0-36CF13-2PS6B2A10-S
GI19987	MG01X4W1-20SKR3-3PS6B2A10-S

Part No.	Model No.
GI19988	MG01X4W0-20UKR3-2PS6B2A10-S
GI19989	MG01X4W0-20SKR3-2PS6B2A10-S
GI30078L	MG03E1R1-08P443-3PS6C2H10-S
GI39990	MG03E4W0-20SKR3-2PS6B2A10-S
I10004L	MN01X4W1-36PT68-3PS6B0A10-S
I10005L	MN01X4W0-41ML59-2TL21A0A10-S
I10006L	MN01X4W0-42PZ68-2TL21A0A10-S
I10007L	MN01X4W1-30PN68-3TL21A0A10-S
I10008L	MN01X4W1-30PN68-3TL15A0A10-S
I10009L	MN01X4W1-30PN68-4CS15A0A10-S
I10011L	MN01X4W1-30PN63-3PS56B0A10-S
I10012L	MN01X4W1-30PN63-3TL56A0A10-S
I10015L	MN01X8W1-24PBB8-5CS15A0A10-S
I10016L	MN01X8W1-24PBB8-6PS15B0A10-S
I10017L	MN01X8W1-24P6H8-5CS15A0A10-S
I10018L	MN01X8W1-24P6H8-6PS15B0A10-S
I10021L	MN01X9W1-30L138-5CS15A0A10-S
I10022L	MN01X9W1-30L138-6PS15B0A10-S
I10023L	MN01X9W1-48PZB8-5CS15A0A10-S
I10024L	MN01X9W1-48PZB8-6PS15B0A10-S
I10025L	MN01X9W1-48L138-5CS15A0A10-S
I10026L	MN01X9W1-48L138-6PS15B0A10-S
I10029L	MN01X9W1-48MI18-6PS6B0A10-S
I10032	MN01X4W1-42IZ68-3TL15A0A10-S
I10033	MN01X4W1-42IZ68-3TL21A0A10-S
I10036	MN01X4W1-38MP19-3TL21A0A10-S
I10037	MN01X4W1-48C133-3PS56B0A10-S
I10038L	MN01X4B1-24PBB3-3PS56B0A10-S
I10045L	MN01X8W1-24PBB8-6PS15D0A10-S
I10046L	MN01X8W1-24P6H8-6PS15D0A10-S
I10047L	MN01XDR1-15P3B8-6PS15D0H10-S
I10048L	MN01X9W1-30L138-6PS15D0A10-S
I10049L	MN01X9W1-48PZB8-6PS15D0A10-S
I10050L	MN01X9W1-48L138-6PS15D0A10-S



Part No.	Model No.
I10051L	MN01X8W1-24PH68-6PS6D0A10-S
I10052L	MN01X9W1-48MI18-6PS6D0A10-S
I10057L	MN01D4W1-36PT68-3PS6B0A10-S
I10059L	MN01D4W0-42PZ68-2TL21A0A10-S
I10060L	MN01D4W1-30PN68-3TL21A0A10-S
I10061L	MN01D4W1-30PN68-3TL15A0A10-S
I10062L	MN01D4W1-30PN68-4CS15A0A10-S
I10064L	MN01D4W1-30PN63-3PS56B0A10-S
I10065L	MN01D4W1-30PN63-3TL56A0A10-S
I10067L	MN01D8W1-24PBB8-5CS15A0A10-S
I10068L	MN01D8W1-24PBB8-6PS15B0A10-S
I10069L	MN01D8W1-24P6H8-5CS15A0A10-S
I10070L	MN01D8W1-24P6H8-6PS15B0A10-S
I10073L	MN01D9W1-30L138-5CS15A0A10-S
I10074L	MN01D9W1-30L138-6PS15B0A10-S
I10075L	MN01D9W1-48PZB8-5CS15A0A10-S
I10077L	MN01D9W1-48L138-5CS15A0A10-S
I10078L	MN01D9W1-48L138-6PS15B0A10-S
I10079L	MN01D9W1-42PTB3-5PS56B0A10-S
I10081L	MN01D9W1-48MI18-6PS6B0A10-S
I10084	MN01D4W1-42IZ68-3TL15A0A10-S
I10085	MN01D4W1-42IZ68-3TL21A0A10-S
I10088	MN01D4W1-38MP19-3TL21A0A10-S
I10089	MN01D4W1-48C133-3PS56B0A10-S
I10090L	MN01D4B1-24PBB3-3PS56B0A10-S
I10091L	MN01D8W1-24PBB8-6PS15D0A10-S
I10092L	MN01D8W1-24P6H8-6PS15D0A10-S
I10093L	MN01DDR1-15P3B8-6PS15D0H10-S
I10094L	MN01D9W1-30L138-6PS15D0A10-S
I10095L	MN01D9W1-48PZB8-6PS15D0A10-S
I10096L	MN01D9W1-48L138-6PS15D0A10-S
I10097L	MN01D8W1-24PH68-6PS6D0A10-S
I10098L	MN01D9W1-48MI18-6PS6D0A10-S
I10103L	MN01X1R1-10L138-3TL6A0H10-S

Part No.	Model No.
I10106L	MN01X1R1-06L198-3TL15A0H10-S
I10107L	MN01X1R1-06L198-4CS15A0H10-S
I10108L	MN01X1R1-06L193-3TL56A0H10-S
I10109L	MN01X1R1-06L193-3PS56B0H10-S
I10117L	MN01D1R1-06L198-3TL15A0H10-S
I10118L	MN01D1R1-06L193-3TL56A0H10-S
I10119L	MN01D1R1-06L193-3PS56B0H10-S
I10120L	MN01D1R1-06L198-4CS15A0H10-S
I10126L	MN01X4B0-30PN63-2TL56A0A10-S-A
I10127L	MN01X4W1-30PN68-3TL15A0A10-S-A
I10128L	MN01X4W1-30PN68-4CS15A0A10-S-A
I10130L	MN01X4W1-30PN63-3TL56A0A10-S-A
I10131L	MN01X4W1-30PN63-3PS56B0A10-S-A
I10133L	MN01X5W1-42PZ68-3TL15A0A10-S-A
I10134L	MN01X5W1-42PZ68-4CS15A0A10-S-A
I10135L	MN01X5W1-44MJ89-3TL21A0A10-S-A
I10136L	MN01X5W1-42PZ63-3TL56A0A10-S-A
I10137L	MN01X5W1-42PZ63-3PS56B0A10-S-A
I10138L	MN01D4B0-30PN63-2TL56A0A10-S-A
I10139L	MN01D4W1-30PN68-3TL15A0A10-S-A
I10140L	MN01D4W1-30PN68-4CS15A0A10-S-A
I10142L	MN01D4W1-30PN63-3TL56A0A10-S-A
I10143L	MN01D4W1-30PN63-3PS56B0A10-S-A
I10145L	MN01D5W1-42PZ68-3TL15A0A10-S-A
I10146L	MN01D5W1-42PZ68-4CS15A0A10-S-A
I10148L	MN01D5W1-42PZ63-3TL56A0A10-S-A
I10149L	MN01D5W1-42PZ63-3PS56B0A10-S-A
I10151L	MN01D2R0-18PB63-2PS56B0H10-S
I10153L	MN01D4B0-30PN63-2PS56B0A10-S-A
I10154	MN01D4B0-42IZ63-2PS56B0A10-S
I10159L	MN01X2R0-18PB63-2PS56B0H10-S
I10161L	MN01X4B0-30PN63-2PS56B0A10-S-A
I10162	MN01X4B0-42IZ63-2PS56B0A10-S
I10483	MN01XGW1-30CF18-6PS15B0A10-S-A



Part No.	Model No.
I10484	MN01XGW1-30CF18-6PS15D0A10-S-A
I10486	MN01X4B0-36CF13-2PS56B0A10-S-A
I10489	MN01X4W1-36CF18-4CS15A0A10-S-A
I10490	MN01X4W1-36CF13-3PS56B0A10-S-A
I10492	MN01DGW1-30CF18-6PS15B0A10-S-A
I10493	MN01DGW1-30CF18-6PS15D0A10-S-A
I10495	MN01D4B0-36CF13-2PS56B0A10-S-A
I10498	MN01D4W1-36CF18-4CS15A0A10-S-A
I10499	MN01D4W1-36CF13-3PS56B0A10-S-A
P110001	MP01X4W1-42IZ68-3JL6A5A10-S
P110003L	MP01X4W1-36PT68-3JL6A5A10-S
P110004L	MP01D4W1-36PT68-3JL6A5A10-S
P110005L	MP01D4W1-30PN68-3JL15A5A10-S
P110006L	MP01D4W0-42PZ67-2C20A9A00-S
P110008L	MP01X4W1-30PN68-3JL15A5A10-S
P110010	MP01X4W1-42IZ68-3JL15A5A10-S
P110011	MP01D4W1-42IZ68-3JL15A5A10-S
P110015L	MP01X4W1-30PN68-4CS15A5A10-S
P110016L	MP01D4W1-30PN68-4CS15A5A10-S
P110017L	MP01X8W1-24P6H8-5CS15A5A10-S
P110018L	MP01D8W1-24P6H8-5CS15A5A10-S
P110019L	MP01X8W1-24PBB8-5CS15A5A10-S
P110020L	MP01D8W1-24PBB8-5CS15A5A10-S
P110025L	MP01X4W1-30PN68-3JL15A5A10-S-A
P110026L	MP01D4W1-30PN68-3JL15A5A10-S-A
P110029L	MP01X4B0-26PJ68-2JL6A5A10-S
P110030L	MP01D4B0-26PJ68-2JL6A5A10-S
P110031L	MP01X4B1-26PJ68-3JL6A5A10-S
P110032L	MP01D4B1-26PJ68-3JL6A5A10-S
UI10007L	MU01D4W0-42PZ67-2C20A9A00-S
UI10022L	DU01X2R1-18PB67-2S02A9F00-S
UI10023L	DU01X4W1-36PNB7-1S02A9K00-S-A

Part No.	Model No.
UI10024L	DU01X4W1-30PN67-2S02A9K00-S-A
UI10025	DU01X4W1-42CF17-1S02A9K00-S-A
UI10026	DU01X1R1-12CF17-1S02A9H00-S
UI10029	DU01X5B1-48CF17-2S02A9K00-S-A
VP3G9100	MG01D1R1-12CF13-3PS6B2H10-S

Vertiv.com | Vertiv Headquarters, 505 N Cleveland Ave, Westerville, OH 43082, USA

© 2025 Vertiv Group Corp. All rights reserved. Vertiv™ and the Vertiv logo are trademarks or registered trademarks of Vertiv Group Corp. All other names and logos referred to are trade names, trademarks or registered trademarks of their respective owners. While every precaution has been taken to ensure accuracy and completeness here, Vertiv Group Corp. assumes no responsibility, and disclaims all liability, for damages resulting from use of this information or for any errors or omissions. Specifications, rebates and other promotional offers are subject to change at Vertiv's sole discretion upon notice.